

DC.SPL.0400.0035



Low voltage DC cable splitter

High quality multi-plug cable splitter for low-voltage applications. The splitter is based on reliable cooper wires for high load and low voltage dropout.



TECHNICAL SPECIFICATION

Parameter	Value	Notes
Type	DC.SPL.0400.0035	1 DC socket to 3 plugs
DC plug size	2.1 × 5.5 mm	3 × plugs
Maximum load	5 A	
Insulation withstand voltage	500 VDC	
DC socket dimension	2.1 × 5.5 mm	1 × socket
Rated voltage	48 VDC	
Wire core diameter	2 × 0.5 mm ²	
Cable outer diameter	2 × 2 mm	Flat type
Operating temperature range	-20°C to +70°C	
Cable length	300 mm	
ROHS	Compliant	

