





L(Length)	T(Tolerance)	Part number	Color
3000	50	SN23-3/10/3GY	GRY
5000	50	SN23-3/10/5GY	GRY



NOTE :

1. PLUG : LT-318(3A) UNITED KINGDOM TYPE
2. CONNECTOR : LT-501 IEC 60320 C13
3. Strain relief : NA
4. CORD : H05VV-F 3X1.0mm²
5. APPROVALS : BSI
6. CUSTOMER : TME
7. Supplier for flexible cord : I-SHENG, LIAN DUNG
8. P/N : Above Note Chart

※Customer drawing number : NA

修改履歷

6		
5		
4		
3		
2		
1	新增	22/09/28
REV.	DESCRIPTION	DATE

DRAWER	Aaron	DATE	22/09/28	TITLE	LT-318+501
APPROVE		REV.	1	Dr.No.	1110965
		比例		TOL.	±5mm
		ALL DIMENSIONS IN mm			



LIAN DUNG
ELECTRIC WIRE MATERIAL CO.,LTD.
聯東電線材料股份有限公司