

LOPPING & FELLING



Legend Bypass Loppers

Fully forged, hardened and tempered special steel blades. Barbed tangs. Lacquered hardwood handles.

Item Number				
G5043	750mm (29 1/2")	45mm (1 1/2")	1.8kg	1



Maxima Telescopic Loppers

Power lever cutting action provides clean, easy cuts. Non-stick coated and chrome plated blades for low friction use and resistance to rust. Precision ground, hardened carbon steel blades. Extendable tubular steel handles with soft, non-slip grips. Fully adjustable blade tension to reduce jarring.

Item Number				
G5014	660 to 990mm (26" to 39")	35mm (1 3/8")	1.8kg	6



Legend Power Loppers

Bypass loppers for green/soft wood. Fully forged, hardened and tempered special steel blades. Barbed tangs and deep ferrules. Wood and rubber buffers to prevent jarring. Lacquered hardwood handles.

Item Number				
G5028	660mm (26")	30mm (1 1/4")	1.2kg	1



Maxima Heavy Duty Bypass Loppers

Heavy duty loppers ideal for tougher wood. Non-stick coated and chrome plated blades for low friction use and resistance to rust. Precision ground, hardened carbon steel blades. Fully adjustable blade tension. Shock absorbing buffer.

Item Number				
G5013	730mm (28 3/4")	30mm (1 1/2")	1.2kg	6



Legend Heavy Duty Anvil Loppers

Anvil cut with cantilever action increases power and reduces effort by 'drawing' the cut. Fully forged, hardened and tempered special steel blades. Non-stick coated blade. Barbed tangs. Lacquered hardwood handles.

Item Number				
G5042	720mm (28")	50mm (2")	1.6kg	1



Maxima Light Weight Bypass Loppers

Compact size allows easy, fatigue free, two handed cutting of small branches. Precision ground, hardened carbon steel blades. Tubular steel handles with soft, non-slip grips. Fully adjustable blade tension. Shock absorbing buffer to reduce jarring.

Item Number				
G5012	480mm (19")	25mm (1")	881g	6