



Maxima Bypass Pruners

Lightweight, pocket sized pruner ideal for delicate pruning work. Non-stick coated and chrome plated blades for low friction use and resistance to rust. Fully adjustable blade tension. Thumb-control safety catch. Two component handles.

Item Number				
G5635	190mm (7 1/2")	16mm (5/8")	175g	3



Pruning Knife

Pruning knife with brass riveted plastic scales. Fine polished, blade with flat back.

Item Number				
G9066	95mm (3 3/4")	55g		3



Maxima Pruning Snips

Ideal for delicate pruning work. Lightweight, easy to use snips for dead heading, vine pruning and other precise tasks. Non-stick coated and chrome plated blades for low friction use and resistance to rust. Fully adjustable blade tension. Two component handles.

Item Number				
G5634	200mm (8")	10mm (3/8")	175g	3



Long Pruning Saw

Precision, taper ground, razor sharp teeth cut on both push and pull strokes without clogging. Comfortable, cushioned handle. Robust holster with belt loop.

Item Number				
G0923	460mm (18 1/2")	446g		3



Locking Pruning Knife

Pruning knife with brass riveted plastic scales and locking function. Fine polished, blade with flat back.

Item Number				
G9068L	110mm (4 1/4")	70g		3



Foldaway Pruning Saw

Precision, taper ground, razor sharp teeth cut on both push and pull strokes without clogging. Comfortable, cushioned handle. Secure safety catch.

Item Number				
G0922	400mm (15 3/4")	200g	-	6
G0920	-	-	Spare blade	3