

# PRODUCT SPECIFICATION

**Carl  
Kammerling**  
International

|                         |                                                       |
|-------------------------|-------------------------------------------------------|
| <b>Brand</b>            | C.K                                                   |
| <b>Product Range</b>    | Trimming Knives                                       |
| <b>Catalogue number</b> | T0951, T0952, T0953-10, 957, 956, 959, 958, 971 & 969 |
| <b>Date</b>             | 30/07/2007                                            |

|                                                                                                                                                                                                                                                        |                                                                                       |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| <b>Range Description</b><br>Professional quality trimming knives and blades                                                                                                                                                                            |                                                                                       |
| <b>Features</b>                                                                                                                                                                                                                                        |                                                                                       |
| <b>951</b> <ul style="list-style-type: none"><li>• Softgrip handle for comfort and control</li><li>• Integral storage for up to 6 blades</li><li>• Integrated blade safety snapper</li><li>• Supplied with 4 blades</li><li>• Display packed</li></ul> |    |
| <b>952</b> <ul style="list-style-type: none"><li>• Softgrip handle for comfort and control</li><li>• Integral storage for up to 6 blades</li><li>• Integrated blade safety snapper</li><li>• Supplied with 4 blades</li><li>• Display packed</li></ul> |  |
| <b>953-10</b> <ul style="list-style-type: none"><li>• Pack of 10 Spare blades for 958</li></ul>                                                                                                                                                        |  |

**957-1**

- Retractable blade for safety
- Softgrip handle for comfort and control
- Magnetic blade retainer for easy blade change
- Captive body screw – can't be lost during blade change
- String/wire cut notch
- Supplied with 10 blades in a safety dispenser
- Display packed

**957-2**

- Softgrip handle for comfort and control
- Magnetic blade retainer for easy blade change
- Captive body screw – can't be lost during blade change
- Supplied with 10 blades in a safety dispenser
- Display packed

**956-1**

- Magnetic blade retainer for easy blade change
- Captive body screw – can't be lost during blade change
- String/wire cut notch
- Supplied with 10 blades in a safety dispenser
- Display packed

**956-2**

- Magnetic blade retainer for easy blade change
- Captive body screw – can't be lost during blade change
- String/wire cut notch
- Display packed Display packed



**959-10**

- 10 Heavy duty blades
- Safety dispenser
- Display packed

**959-50**

- 50 Heavy duty blades
- Safety dispenser
- Display packed

**959-100**

- 100 Heavy duty blades
- Safety dispenser
- Display packed

**958**

- Softgrip handle for comfort and control
- Integral storage for up to 6 blades
- Integrated blade safety snapper
- Supplied with 4 blades
- Display packed

**971-10**

- Pack of 10 Spare blades for 958

**969**

- Auto retracting blade for safety



| Item Number | Item Description                                            | EAN No        | Commodity code | Shelf box Qty |
|-------------|-------------------------------------------------------------|---------------|----------------|---------------|
| T0951       | C.K Trimming Knife 9mm snap-off                             | 5013969699975 | 82119300       | 6             |
| T0952       | C.K Trimming Knife, die-cast, 9mm snap-off                  | 5013969699982 | 82119300       | 6             |
| T0953-10    | C.K Trimming Knife blades, 9mm snap-off (pack of 10 pieces) | 5013969699999 | 82119400       | 6             |
| T0957-1     | C.K Trimming Knife Soft Grip Retracting                     | 5013969700039 | 82119300       | 6             |
| T0957-2     | C.K Trimming Knife Soft Grip Non Retracting                 | 5013969700046 | 82119300       | 6             |
| T0956-1     | C.K Trimming Knife Retracting                               | 5013969700015 | 82119300       | 6             |

|           |                                                               |               |          |    |
|-----------|---------------------------------------------------------------|---------------|----------|----|
| T0956-2   | C.K Trimming Knife Non Retracting                             | 5013969700022 | 82119300 | 6  |
| T0959-10  | C.K Spare Trimming Knife Blades Pack Of 10                    | 5013969700060 | 82119400 | 12 |
| T0959-50  | C.K Spare Trimming Knife Blades Pack Of 50                    | 5013969700077 | 82119400 | 12 |
| T0959-100 | C.K Spare Trimming Knife Blades Pack Of 100                   | 5013969700084 | 82119400 | 12 |
| T0958     | C.K Trimming Knife With Snap Off Blade                        | 5013969700053 | 82119300 | 12 |
| T0971-10  | C.K Spare Trimming Knife Blades Snap Off For T0958 Pack Of 10 | 5013969700329 | 82119400 | 12 |
| T0969     | C.K Trimming knife auto retracting                            | 5013969062786 | 82119300 | 6  |

|                                    |                                                                                                                                        |
|------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------|
| Technical product information      |                                                                                                                                        |
| Standards compliance               | None applicable                                                                                                                        |
| User health and safety information | Users are advised to wear safety goggles                                                                                               |
| RoHS/WEEE compliance               | This product range does not fall within the scope of RoHS or WEEE regulations                                                          |
| Material safety data               | Not applicable                                                                                                                         |
| Warranty                           | C.K tools are guaranteed for life against imperfect materials or workmanship<br>Damage caused through inappropriate use is not covered |
| Country of origin                  | T0951 / T0952 / T0953-10 - China<br>All others – Taiwan                                                                                |

## Dimensional details

|           | Product only |          |           |              | Product on primary packaging |          |           |                |
|-----------|--------------|----------|-----------|--------------|------------------------------|----------|-----------|----------------|
| Item      | Width mm     | Depth mm | Height mm | Net weight g | Width mm                     | Depth mm | Height mm | Gross weight g |
| T0951     |              |          |           |              | 195                          | 62       | 15        | 36             |
| T0952     |              |          |           |              | 190                          | 62       | 20        | 106            |
| T0953-10  |              |          |           |              | 160                          | 60       | 10        | 300            |
| T0957-1   | 40           | 23       | 150       | 110          | 120                          | 23       | 193       | 167            |
| T0957-2   | 35           | 23       | 135       | 83           | 120                          | 23       | 177       | 140            |
| T0956-1   | 40           | 23       | 150       | 98           | 120                          | 23       | 193       | 155            |
| T0956-2   | 35           | 23       | 135       | 72           | 120                          | 23       | 177       | 129            |
| T0959-10  | 25           | 15       | 68        | 44           | 66                           | 16       | 120       | 54             |
| T0959-50  | 65           | 28       | 115       | 224          | 113                          | 33       | 175       | 251            |
| T0959-100 | 65           | 28       | 115       | 402          | 113                          | 33       | 175       | 429            |
| T0958     | 50           | 25       | 165       | 174          | 90                           | 28       | 213       | 198            |
| T0971-10  | 23           | 13       | 118       | 75           | 66                           | 15       | 185       | 90             |

|       |    |    |     |    |    |    |     |     |
|-------|----|----|-----|----|----|----|-----|-----|
| T0969 | 35 | 23 | 150 | 87 | 93 | 27 | 235 | 112 |
|-------|----|----|-----|----|----|----|-----|-----|

| Item      | Shelf box (secondary packaging) |          |           |                               | Euro Pallet data<br>Wi x Hi |                     |
|-----------|---------------------------------|----------|-----------|-------------------------------|-----------------------------|---------------------|
|           | Width mm                        | Depth mm | Height mm | Gross weight g<br>Inc product | No of cartons on base       | Number of rows high |
| T0957-1   | 140                             | 250      | 115       | 1170                          |                             |                     |
| T0957-2   | 140                             | 250      | 115       | 1008                          |                             |                     |
| T0956-1   | 140                             | 250      | 115       | 1098                          |                             |                     |
| T0956-2   | 140                             | 250      | 115       | 942                           |                             |                     |
| T0959-10  | 130                             | 260      | 90        | 730                           |                             |                     |
| T0959-50  | 255                             | 360      | 70        | 2890                          |                             |                     |
| T0959-100 | 255                             | 360      | 70        | 2890                          |                             |                     |
| T0958     | 140                             | 250      | 115       | 5026                          |                             |                     |
| T0971-10  | 130                             | 260      | 90        | 1208                          |                             |                     |
| T0969     | 130                             | 265      | 85        | 768                           |                             |                     |

## Packaging waste details

| Item      | Primary Packaging |         |        |      | Secondary packaging |     |        |     |
|-----------|-------------------|---------|--------|------|---------------------|-----|--------|-----|
|           | Plastic g         | Use     | Card g | Use  | Plastic g           | Use | Card g | Use |
| T0957-1   | 3                 | Blister | 10     | Card |                     |     | 168    | Box |
| T0957-2   | 3                 | Blister | 10     | Card |                     |     | 168    | Box |
| T0956-1   | 3                 | Blister | 10     | Card |                     |     | 168    | Box |
| T0957-1   | 3                 | Blister | 10     | Card |                     |     | 168    | Box |
| T0959-10  | 4                 | Blister | 6      | Card |                     |     | 114    | Box |
| T0959-50  | 12                | Blister | 15     | Card |                     |     | 202    | Box |
| T0959-100 | 12                | Blister | 15     | Card |                     |     | 202    | Box |
| T0958     | 9                 | Blister | 15     | Card |                     |     | 168    | Box |
| T0971-10  | 6                 | Blister | 9      | Card |                     |     | 114    | Box |
| T0969     | 8                 | Blister | 17     | Card |                     |     | 95     | Box |