

PRODUCT SPECIFICATION

Brand	C.K
Product Range	Waterpump pliers
Catalogue number	3651, 3655, 3659A & 3629A
Date	24/08/2012

Range Description Waterpump pliers	
Features Speedlok • Special alloy steel, drop forged, hardened & tempered for exceptional strength & durability. • Induction hardened jaws for outstanding long term performance. • 'Slide to adjust' mechanism for fast & accurate size adjustment. • Slim head & jaws for access to confined spaces. • Contoured anti-slip handles for comfortable & powerful operation Waterpump pliers – heavy duty • Special alloy steel, drop forged, hardened & tempered for exceptional strength & durability. • Induction hardened jaws for outstanding long term performance. • Box joint design with double pivot support for strength. • Slim head & jaws for access to confined spaces. • Contoured anti-slip handles for comfortable & powerful operation. Waterpump pliers – Standard • Special alloy steel, drop forged, hardened & tempered for exceptional strength & durability. • Induction hardened jaws for outstanding long term performance. • Non slip groove joint. • Slim head & jaws for access to confined spaces. • Contoured anti-slip handles for comfortable & powerful operation.	 3655  3659A  3651

Waterpump pliers – 400mm • Special alloy steel, drop forged, hardened & tempered for exceptional strength & durability. • Induction hardened jaws for outstanding long term performance. • Non slip groove joint. • Slim head & jaws for access to confined spaces. • Contoured anti-slip handles for comfortable & powerful operation.		 3629A		
Item Number	Item Description	EAN No	Commodity code	Shelf box Qty
T3651 09	Waterpump pliers 250mm	5013969489309	82032090	3
T3655 250	Speedlok waterpump pliers 250mm	5013969984790	82032090	3
T3655 300	Speedlok waterpump pliers 300mm	5013969984806	82032090	3
T3659A 175	Waterpump pliers 175mm	5013969972368	82032090	3
T3659A 240	Waterpump pliers 250mm	5013969601008	82032090	3
T3659A 300	Waterpump pliers 300mm	5013969331509	82032090	3
T3629A 400	Waterpump pliers 400mm	5013969008722	82032090	1

Technical product information	
Standards compliance	DIN ISO 8976
User health and safety information	Non applicable
RoHS/WEEE compliance	These product ranges do not fall within the scope of RoHS or WEEE regulations
Material safety data	Not applicable
Warranty	C.K tools are guaranteed for life against imperfect materials or workmanship Damage caused through inappropriate use is not covered
Country of origin	3655 / 3651 / 3659 – Germany 3629A – Taiwan

Dimensional details

	Product only				Product on primary packaging			
Item	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T3651 09	54	20	260	348	65	25	315	362
T3655 250	55	15	255	330	60	25	310	344
T3655 300	70	15	330	625	70	25	385	639
T3659A 175	37	12	180	169	60	25	250	183
T3659A 240	40	15	240	334	60	25	320	348
T3659A 300	55	17	300	612	67	25	365	626
T3629A 400	90	20	420	1098	90	25	430	1112

	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
Item	Width mm	Depth mm	Height mm	Gross weight g Inc product	No of cartons on base	Number of rows high
T3651 09	145	390	40	1180		
T3655 250	145	390	40	1126		
T3655 300	85	380	60	2011		
T3659A 175	85	225	70	607		
T3659A 240	163	377	40	1140		
T3659A 300	163	377	40	1974		
T3629A 400	130	470	20	1118		

Packaging waste details

	Primary Packaging				Secondary packaging			
Item	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T3651 09	14	Hanger					94	Box
T3655 250	14	Hanger					94	Box
T3655 300	14	Hanger					94	Box
T3659A 175	14	Hanger					58	Box
T3659A 240	14	Hanger					96	Box
T3659A 300	14	Hanger					96	Box
T3629A 400	14	Hanger			6	Bag		