

Product information

90 23 01 BK

KNIPEX DP50

Pipe Cutter for plastic drain pipes



- Cut and chamfer all common domestic plastic drain pipes up to Ø 50 mm in a single operation
- Reversible high-quality ball-bearing steel blade, can be easily replaced without tools
- Clean cut: no readjusting or deburring required, reducing potential blockages or damages of the seals
- Cuts high temperature and other plastic pipes with Ø 32, 40 or 50 mm and wall thicknesses up to 2.4 mm
- Optimal cutting due to slide-bearing and self-adjusting guide rolls
- Easy positioning due to clear view of cutting point
- Spring-loaded blade: no inconvenient readjusting while cutting
- Exchangeable blade with two cutting edges can be reversed when showing signs of wear
- Cuts lengths as small as 10 mm
- Durable housing made of glass fibre reinforced plastic

General

Article No.	90 23 01 BK
EAN	4003773087809
Handles	plastic coated
Weight	295 g
Dimensions	202 x 40 x 19 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

technical change and errors excepted















