


Flexible Ring Socket Wrench & Set

3350M
 3/8"

- Flexible head folds up to 200°
- Combined with F-handle, handle, T-handle speed-handle
- Suitable for all hydraulic, fuel, oil brake, A/C, auto tool and air line work
- DIN 3120




KT NO.	 mm	D1 mm	D2 mm	L mm		
335008M	8	15.0	18.8	45.0	44	12 / 360
335009M	9	18.0	18.8	49.0	48	12 / 360
335010M	10	18.0	18.8	49.0	49	12 / 360
335011M	11	22.0	18.8	53.0	58	12 / 360
335012M	12	22.0	18.8	53.0	58	12 / 360
335013M	13	26.0	18.8	60.0	80	12 / 240
335014M	14	26.0	18.8	60.0	82	12 / 240
335015M	15	27.0	18.8	60.0	80	12 / 240
335016M	16	32.0	24.7	73.5	159	6 / 96
335017M	17	33.0	24.7	73.5	159	6 / 96
335018M	18	33.0	24.7	73.5	156	6 / 96
335019M	19	32.0	24.7	73.5	161	6 / 96

Flexible Crowfoot Socket Wrench & Set

3351M
 3/8"

- Flexible head folds up to 200°
- Combined with F-handle, handle, T-handle speed-handle
- Suitable for all hydraulic, fuel, oil brake, A/C, auto tool and air line work
- DIN 3120



KT NO.	 mm	D1 mm	D2 mm	L mm		
335108M	8	15.0	18.8	45.0	45	12 / 360
335109M	9	18.0	18.8	49.0	48	12 / 360
335110M	10	18.0	18.8	49.0	49	12 / 360
335111M	11	22.0	18.8	53.0	57	12 / 360
335112M	12	22.0	18.8	53.0	57	12 / 360
335113M	13	26.0	18.8	60.0	77	12 / 240
335114M	14	26.0	18.8	60.0	76	12 / 240
335115M	15	27.0	18.8	60.0	76	12 / 240
335116M	16	32.0	24.7	73.5	153	6 / 96
335117M	17	33.0	24.7	73.5	152	6 / 96
335118M	18	33.0	24.7	73.5	150	6 / 96
335119M	19	33.3	24.7	73.5	153	6 / 96

3609MR10
 3/8"

- Socket rail 290mmL



Contents		
  3350M 8, 10, 12, 13, 14, 16, 17, 18, 19	0.99	20
8731109		

3619MR10
 3/8"

- Socket rail 290mmL



Contents		
  3351M 8, 10, 12, 13, 14, 16, 17, 18, 19	0.89	20
8731109		

3612MR
 3/8"

Metal case size (mm):
296 x 130 x 41 (0.056 cuft)

Contents		
  3351M 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19	1.89	1 / 10


12 PC.