

Sealing profile side 4,0-6,0 RAL 9005 Black coil 50m

SKU	MCB013AB12
EAN	4744397012159
Color	Black
Material	PVC, EPDM
Item width (mm)	16
Item length (mm)	50000
Item height (mm)	33
Item weight (g)	15500
Clamping range (mm)	4...6
Plate thickness (mm)	4...6
Minimum bending radius	A = 80, B = 80, C = 140, D = 140Min. 1000 m / order
CN8 code	39169090
Package quantity (pcs)	50

