

FK-566-GF starrer Gegenkontakt | rigid contact terminal**Technische Daten | Technical Data**

Empf. Mindesttrasterabstand rec. centre spacing:	2,54 mm	.100 inches
Temperaturbereich Temperature range:	-55°C bis +250°C	-67°F to +482°F
Typischer Widerstand Typical Resistance:	20 mΩ	20 mΩ
Typischer Nennstrom Rated Current Load:	3 A	3 amps
E-Maß Extension Height:	6,20 mm	.244 inches
Bauform, Anschluss Design, Connection Type:	THT-b	

Werkstoffe | Materials

Messing, vergoldet | Brass, gold plated

