

Tower pincers

531/4PR



Profiles



Product features


- material: premium plus carbon steel
- drop forged, entirely hardened and tempered
- the cutting edges are induction-hardened to 61HRc
- head surface finish: finely ground
- surface finish: phosphated to standard ISO 9717
- handles plastic dipped
- made according to standard ISO 9242

Advantages:

- the precise form of the joint enables the automatic opening of the pincers in a horizontal position, so the force is applied only during cutting of the wires

Usage:

- useful for the binding and cutting of wires



	L	B	A	C	
601386	224	30	23	17	333
601387	250	36	25	18	424
601388	280	36	25	18	455

* Images of products are symbolic. All dimensions are in mm, and weight in grams. All listed dimensions may vary in tolerance.

Related products

 Tower pincers

 Tower pincers

 Heavy duty tower pincers