

Insulated single offset ring wrench

180/2VDEDP



Profiles



Standards

DIN EN IEC 60900 (VDE 0682-201):2019-04; EN IEC 60900:2018

Product features


- material: premium chrome vanadium steel
- head: chrome plated according to ISO 1456:2009
- made according to standard ISO 10104 and EN IEC 60900:2018

Advantages:

- double layered - double coloured insulation for additional safety
- controlled according to standard EN IEC 60900

Important!

- if second layer is visible, replace your insulated tool with a new one.



		L	B	A	
621580	6	155	13.5	8.5	51
621581	7	155	15	9	57
621582	8	160	16.5	9.5	62
621583	9	160	17.5	10	72
612185	10	162	19.5	11	81
612186	11	175	20	11.5	97
612187	12	185	21.5	11.5	112
612188	13	185	23	12.5	113
612189	14	190	25.5	13	136
612190	15	195	27	13.5	146
621584	16	190	27.5	14.5	175
612191	17	208	30.5	15.5	185
621585	18	195	30	15.5	210
612192	19	227	33	15.5	233
621586	20	245	34.5	16.2	273
619202	21	244	36.4	13.2	307
612193	22	250	37.5	17.5	300
621587	23	250	39.8	16.8	333
612194	24	255	42	18.5	428
621588	26	265	44	18	450
621589	27	270	44.8	18	411
621590	28	280	36.5	18.5	488
621591	30	310	47	19	574
621592	32	325	51.5	19.5	647

* Images of products are symbolic. All dimensions are in mm, and weight in grams. All listed dimensions may vary in tolerance.