





MODEL NO.	SWITCH FUNCTION			TERMINAL QUANTITY	CONNCTED TERMINALS		
	POS.1	POS.1	POS.1		POS.1	POS.1	POS.1
T7A23	ON	OFF	ON	6P	1-2 4-5	—	2-3 5-6
T7A26	MM	OFF	ON	6P	1-2 4-5	—	2-3 5-6
T7A27	MM	OFF	MM	6P	1-2 4-5	—	2-3 5-6
T7A22	ON	NONE	ON	6P	1-2 4-5	—	2-3 5-6

MM=MOMENTARY

SPECIFICATION

- 1.PATING:10A 250VAC,15A 125VAC (UL, CUL)
- 2.INSULATION RESISTANCE:DC 500V 200MΩ OR MORE
- 3.CONTACT RESISTANCE:DC 2-4V 1A 20MΩ OR LESS
- 4.WITHSTAND VOLTAGE:AC 1500V OR MORE

端子種類尺寸 Termination Options

H1	H2	H3	H4	H5

REVISION	DESCRIPTION	REVISED BY	TOLERANCES .X .XX		ANGLE 1/2°	UNIT	mm	PART NAME	SPEC DRAWING (6PIN)	DWG NO
△			DRAWN BY	張俊雄	DESIGNED BY	王豐文	SCALE			WS2613C
△2017.03.13	修正RATING	張俊雄	CHECKED BY	Jimmy	APPROVED BY		DATE	2015.01.16	PART NO	
△2015.09.16	增加功能選項	張俊雄								
△2015.01.16	首次出圖	張俊雄								