



BE-8715 - BE-8710

**ERGO™ Hex Ball End
Screwdrivers with Rubber Grip,
metric 1.5-10 mm**



PRODUCT DETAILS

- Screwdriver developed according to the scientific ERGO™ process
- For hexagonal head screws, ball end, easy to insert in the screw head from a range of angles
- For more efficient work than the standard hexagonal and time saver
- Black oxide tip for higher accuracy
- Three-component handle for maximum user comfort, soft material with ridged surface provides superior grip and greater force transmission
- Maximum comfort with minimum effort thanks to an ergonomic design
- Easy to choose the right tip with the colour-coded handle and permanent symbol on the domed end
- No colour identification in extra small handle, small sizes 1.5, 2.0, 2.5
- Flat face to prevent rolling away
- Integrated hanging hole
- Size 10, in double shape handle for use with both hands for maximum torque power
- High performance steel blade with chrome plating for high protection against corrosion, long life tool
- Standards: ISO 2936



Follow the Fish!



PRODUCT ATTRIBUTES

Product							
BE-8715	1.5 mm	60 mm	3 mm	17 mm	103 mm	163 mm	30 g
BE-8702	2 mm	100 mm	3 mm	17 mm	103 mm	203 mm	32 g
BE-8725	2.5 mm	100 mm	3 mm	17 mm	103 mm	203 mm	32 g
BE-8703	3 mm	100 mm	3.5 mm	20 mm	122 mm	222 mm	35 g
BE-8704	4 mm	100 mm	5 mm	27 mm	122 mm	222 mm	66 g
BE-8705	5 mm	100 mm	6 mm	36 mm	122 mm	222 mm	105 g
BE-8706	6 mm	125 mm	7 mm	36 mm	122 mm	247 mm	125 g
BE-8708	8 mm	150 mm	10 mm	36 mm	122 mm	272 mm	197 g
BE-8710	10 mm	150 mm	12 mm	36 mm	161 mm	311 mm	250 g

Follow the Fish!

