


Cable ties:
TY271 series



Product selection

Part no. standard GID no.	Color	Min. Bundle diameter inch (mm)	Max. Bundle diameter inch (mm)	Tensile strength lbs. (N)	A inch (mm) ±0.20 (5.0)	B inch (mm) ±0.010 (0.25)	C inch (mm) ±0.02 (5.0)	D inch (mm) ±0.060 (1.5)	E inch (mm) ±0.010 (0.25)	Minimum Operating Temp. °F (°C)	Maximum Operating Temp. °F (°C)	Minimum Installation Temp. °F (°C)
TY271M 7TCG009450R0162	Natural	0.19 (4.8)	0.98 (25)	54 (240)	5.9 (150)	0.27 (6.9)	0.32 (8.1)	0.48 (12.2)	0.06 (1.5)	-76 (-60)	185 (85)	-4 (-20)
TY5271MR 7TCG009450R0180	Natural											
TY271MX 7TCG009450R0163	UV Black	0.19 (4.8)	0.98 (25)	120 (540)	5.9 (150)	0.27 (6.9)	0.32 (8.1)	0.48 (12.2)	0.06 (1.5)	-76 (-60)	221 (105)	-40 (-40)
TY5271MXR 7TCG009450R0181	UV Black											
TY271MX-RW 7TCG009450R0226	UV Black											
TY5271MXR-RW 7TCG009450R0227	UV Black											

Note: Product must be installed in accordance with applicable national and local electrical codes.

Cable ties:
TY272 series

Product selection

Part no. standard GID no.	Color	Min. Bundle diameter inch (mm)	Max. Bundle diameter inch (mm)	Tensile strength lbs. (N)	A inch (mm) ±0.20 (5.0)	B inch (mm) ±0.010 (0.25)	C inch (mm) ±0.02 (5.0)	D inch (mm) ±0.060 (1.5)	E inch (mm) ±0.010 (0.25)	Minimum Operating Temp. °F (°C)	Maximum Operating Temp. °F (°C)	Minimum Installation Temp. °F (°C)
TY272M 7TAG009340R0002	Natural	0.24 (6.0)	2.01 (51)	120 (540)	8.8 (224)	0.27 (6.9)	0.32 (8.1)	0.50 (12.7)	0.06 (1.5)	-76 (-60)	185 (85)	-4 (-20)
TY5272MR 7TCG009460R0102	Natural											
TY5272M 7TAG009300R0015	Natural											
TY272M-1 7TAG009000R0239	Brown											
TY272M-2 7TAG009370R0001	Red											
TY272M-3 7TAG009370R0003	Orange											
TY272M-4 7TAG009370R0004	Yellow											
TY272M-5 7TAG009370R0005	Green											
TY272M-6 7TAG009370R0007	Blue											
TY272M-7 7TAG009370R0009	Purple											
TY272M-9 7TAG009370R0011	White											
TY272MX 7TAG009330R0007	UV Black	0.19 (4.8)	2.01 (51)	120 (540)	8.8 (224)	0.27 (6.9)	0.32 (8.1)	0.50 (12.7)	0.06 (1.5)	-76 (-60)	185 (85)	-22 (-30)
TY5272MX 7TAG009290R0003	UV Black											
TY5272MXR 7TCG009460R0103	UV Black											
TY5272MXR-RW 7TCG009330R0016	Railway UV Black	0.19 (4.8)	2.01 (51)	120 (540)	8.8 (224)	0.27 (6.9)	0.32 (8.1)	0.50 (12.7)	0.06 (1.5)	-76 (-60)	221 (105)	-40 (-40)
TY272MX-RW 7TAG009330R0008	Railway UV Black											

Note: Product must be installed in accordance with applicable national and local electrical codes.