

PRODUCT-DETAILS

TY175-50X-100

CBL TIE 7IN UV BLACK NYL 50LB



General Information

Extended Product Type	TY175-50X-100
Product ID	7TAG054360R0179
EAN	5414363075165
Catalog Description	CBL TIE 7IN UV BLACK NYL 50LB
Long Description	Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (220 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, Length of 186.43mm (7.34 Inches), Width of 4.674mm (0.184 Inches), Thickness of 1.24mm (0.049 Inches), Tensile Strength Rating of 220 Newtons (50 Pounds), 100 Pack

Ordering

EAN	5414363075165
Customs Tariff Number	3926909990

Dimensions

Product Net Weight	.004 lb 1.814 g
--------------------	--------------------

Container Information

Package Level 1 Units	100 piece
Package Level 1 Width	5 in 127 mm

Package Level 1 Height	1.25 in 32 mm
Package Level 1 Depth / Length	12 in 305 mm
Package Level 2 Units	1000 piece
Package Level 2 Width	8.4 in 213 mm
Package Level 2 Height	6.3 in 160 mm
Package Level 2 Depth / Length	9.8 in 249 mm

Additional Information

Brand / Label	Ty-Fast
Bundle Diameter	1.75 in 44.45 mm
Color	Black
Lock Type	Plastic Pawl
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	PLASTIC CABLE TIE
Product Type	General Purpose
Standards	UL E49405
Tensile Strength	50 lb 222 N
Thickness	0.049 in 1.24 mm
UPC	075114952354

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY175-50X-100
Declaration of Conformity - CE	9AKK107492A9843
Instructions and Manuals	TY175-50X-100

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

