



PRODUCT-DETAILS

TY200-120X

CBL TIE 120LB 9IN UV BLACK NYLON



General Information

Extended Product Type	TY200-120X
Product ID	7TCG054360R0188
EAN	5414363075172
Catalog Description	CBL TIE 120LB 9IN UV BLACK NYLON
Long Description	Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, Length of 200mm (7.87 Inches), Width of 7.6mm (0.30 Inches), Thickness of 1.6mm (0.06 Inches), Tensile Strength Rating of 534 Newtons (120 Pounds), Bulk Pack

Ordering

EAN	5414363075172
UPC	786210292915

Dimensions

Product Net Width	0.3 in 7.62 mm
Product Net Depth / Length	7.87 in 200 mm

Container Information

Package Level 1 Units	500 piece
-----------------------	-----------

Package Level 1 Width	2 in 51 mm
Package Level 1 Height	16 in 406 mm
Package Level 1 Depth / Length	22 in 559 mm
Package Level 2 Units	2500 piece
Package Level 2 Width	10.2 in 259 mm
Package Level 2 Height	9.1 in 231 mm
Package Level 2 Depth / Length	19.7 in 500 mm

Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

Additional Information

Brand / Label	Catamount
Bundle Diameter	2 in 50.8 mm
Color	Black
Effective Date	19950623
Lock Type	Plastic Pawl
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	NYLON CABLE TIE
Product Type	General Purpose
Standards	UL E49405
Tensile Strength	120 lb 540 N
Thickness	0.06 in 1.6 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY200-120X
Declaration of Conformity - CE	9AKK107492A9843
Instructions and Manuals	TY200-120X

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

