



407-4-75/407-14-250 Screwdrivers Slotted



PRODUCT DETAILS

- For slotted head screws
- Sandblasted tip for better screw grip and full anti-rust guarantee
- For intensive use
- Two-component handle for comfortable grip and high torque transfer
- Non-rolling handle shape
- Integrated hanging hole
- High performance alloy steel blade, chrome plated and fully hardened
- Permanently marked blade with size and part number for easy identification
- Standards: ISO 2380, DIN 5264, UNE 16516



PRODUCT ATTRIBUTES

Product								
407-4-75	0.8 mm	4 mm	75 mm	4 mm	26 mm	90 mm	165 mm	40 g
407-4-100	0.8 mm	4 mm	100 mm	4 mm	26 mm	90 mm	190 mm	40 g
407-5.5-100	1 mm	5.5 mm	100 mm	5 mm	30 mm	100 mm	200 mm	65 g
407-5.5-125	1 mm	5.5 mm	125 mm	5 mm	30 mm	100 mm	225 mm	70 g
407-6.5-125	1.2 mm	6.5 mm	125 mm	6 mm	34 mm	110 mm	235 mm	100 g
407-6.5-150	1.2 mm	6.5 mm	150 mm	6 mm	34 mm	110 mm	260 mm	105 g
407-8-150	1.6 mm	8 mm	150 mm	7 mm	34 mm	110 mm	260 mm	119 g
407-8-175	1.6 mm	8 mm	175 mm	7 mm	34 mm	110 mm	285 mm	127 g
407-10-200	1.6 mm	10 mm	200 mm	8 mm	37 mm	120 mm	320 mm	175 g
407-12-250	2 mm	12 mm	250 mm	10 mm	37 mm	120 mm	370 mm	230 g
407-14-250	2.5 mm	14 mm	250 mm	14 mm	37 mm	120 mm	370 mm	260 g