



408V-2.5-100/408V-8-175 Insulated Screwdrivers Slotted



PRODUCT DETAILS

- Insulated VDE screwdriver for slotted head screws
- Phosphate finish tip for higher accuracy
- For working on live equipment up to 1000 V
- Two-component handle for comfortable grip and high torque transfer
- Non-rolling handle shape
- Integrated hanging hole
- High quality blade insulation moulded directly onto the blade for total safety
- Permanently marked blade with size and part number for easy identification
- Individually inspected and manufactured according to IEC 60900, tested in a water bath at 10,000 V
- Standards: ISO 2380, DIN 5264, UNE 16516



PRODUCT ATTRIBUTES

Product							
408V-2.5-100	0.4 mm	2.5 mm	100 mm	26 mm	90 mm	190 mm	20 g
408V-3-100	0.5 mm	3 mm	100 mm	26 mm	90 mm	190 mm	22 g
408V-3.5-100	0.6 mm	3.5 mm	100 mm	26 mm	90 mm	190 mm	32 g
408V-4-100	0.8 mm	4 mm	100 mm	26 mm	90 mm	190 mm	35 g
408V-5.5-125	1 mm	5.5 mm	125 mm	30 mm	100 mm	225 mm	65 g
408V-6.5-150	1.2 mm	6.5 mm	150 mm	34 mm	110 mm	260 mm	90 g
408V-8-175	1.2 mm	8 mm	175 mm	37 mm	120 mm	295 mm	110 g