



414-10-75/414-40-150

Screwdrivers Torx®



PRODUCT DETAILS

- For Torx® head screws
- Black finish tip for higher accuracy
- For intensive use
- Two-component handle for comfortable grip and high torque transfer
- Non-rolling handle shape
- Integrated hanging hole
- High performance alloy steel blade, chrome plated and fully hardened
- Permanently marked blade with size and part number for easy identification



PRODUCT ATTRIBUTES

Product								
414-5-75	T5	1.37 mm	75 mm	2.5 mm	26 mm	90 mm	165 mm	32 g
414-6-75	T6	1.65 mm	75 mm	3 mm	26 mm	90 mm	165 mm	35 g
414-7-75	T7	1.97 mm	75 mm	3 mm	26 mm	90 mm	165 mm	35 g
414-8-75	T8	2.30 mm	75 mm	3 mm	26 mm	90 mm	165 mm	35 g
414-9-75	T9	2.48 mm	75 mm	3 mm	26 mm	90 mm	165 mm	35 g
414-10-75	T 10	2.72 mm	75 mm	3 mm	26 mm	90 mm	165 mm	35 g
414-15-100	T 15	3.26 mm	100 mm	4 mm	26 mm	90 mm	190 mm	45 g
414-20-100	T 20	3.84 mm	100 mm	4 mm	26 mm	90 mm	190 mm	45 g
414-25-125	T 25	4.40 mm	125 mm	6 mm	30 mm	100 mm	225 mm	70 g
414-27-125	T 27	4.96 mm	125 mm	6 mm	30 mm	100 mm	225 mm	70 g
414-30-150	T 30	5.49 mm	150 mm	6 mm	34 mm	110 mm	260 mm	105 g
414-40-150	T 40	6.60 mm	150 mm	7 mm	34 mm	110 mm	260 mm	120 g
414-45-150	T45	7.70 mm	150 mm	8 mm	34 mm	110 mm	260 mm	120 g