



T49T20L-T49T60L

10 mm Long Bits Torx® 115 mm

PRODUCT DETAILS

- For Torx® head screws
- 10 mm hex drive DIN 3126 and ISO 1173 Style C 10
- For the automotive sector
- High performance alloy steel
- Matte chrome plated finish for sockets
- Zinc phosphate finish for bits
- Single pack



PRODUCT ATTRIBUTES

Product					
T49T20L	1	T20	3.84 mm	75 mm	20 g
T49T25L	1	T25	4.4 mm	75 mm	20 g
T49T27L	1	T27	4.96 mm	75 mm	20 g
T49T30L	1	T30	5.49 mm	75 mm	20 g
T49T40L	1	T40	6.6 mm	75 mm	20 g
T49T45L	1	T45	7.7 mm	75 mm	20 g
T49T50L	1	T50	8.79 mm	75 mm	20 g
T49T55L	1	T55	11.17 mm	75 mm	20 g
T49T60L	1	T60	13.2 mm	75 mm	20 g