



T49T20H-T49T60H

10 mm Bits Torx® Tamper 30 mm

PRODUCT DETAILS

- For Torx® Tamper - Resistant head screws with safety pin
- 10 mm hex drive DIN 3126 and ISO 1173 Style C 10
- For the automotive sector
- High performance alloy steel
- Matte chrome plated finish for sockets
- Zinc phosphate finish for bits
- Single pack



PRODUCT ATTRIBUTES

Product					
T49T20H	1	TR20	3.84 mm	30 mm	6.5 g
T49T25H	1	TR25	4.4 mm	30 mm	6.5 g
T49T27H	1	TR27	4.96 mm	30 mm	6.5 g
T49T30H	1	TR30	5.49 mm	30 mm	6.5 g
T49T40H	1	TR40	6.6 mm	30 mm	6.5 g
T49T45H	1	TR45	7.7 mm	30 mm	6.5 g
T49T50H	1	TR50	8.79 mm	30 mm	6.5 g
T49T55H	1	TR55	11.17 mm	30 mm	6.5 g
T49T60H	1	TR60	13.2 mm	30 mm	6.5 g