

1933I

die grinder

CE

- Collect chuck, Ø 3 mm and 6 mm

Free speed	20,000 rpm
Chuck capacity	3 - 6 mm
Power	0,38 kW
Air inlet	1/4" GAS
Working pressure	6,2 bar
Internal hose size (Ø)	10 mm
Mean air consumption	260 l/min
Weight	670 g

	art.	
019330005	1933I	670

