

1934MAV70
High-speed micro die grinder

CE

- High-speed
- Compact, lightweight, for remarkable ease of handling
- Protected 1.5-m-long hose
- 70,000 rpm

70,000 rpm

For precision jobs

0.08 kW

Free speed	70,000 rpm
Chuck capacity	3 mm
Power	0,08 kW
Air inlet	1/4" GAS BSPT
Operating pressure	6,2 bar
Internal hose size (Ø)	4,5 mm
Mean air consumption	115 l/min
Weight	0.21 kg



	art.	
019340030	1934MAV70	210