

1936/4A

Angle grinder

CE

- Extremely compact and handy
- Air governor for automatically controlling top speed
- Right-hand/left-hand auxiliary handle
- Spindle lock button
- Accessory for quickly changing discs
- Safety cap can be quickly adjusted in nine different positions through quick release

Free speed	11,000 rpm
Grinding disc size	115 mm
Power	0,66 kW
Spindle thread	M14
Air inlet	1/4" GAS
Operating pressure	6.2 bar
Internal hose size (Ø)	10 mm
Mean air consumption	390 l/min
Weight	1.77 kg

	art.	
019360024	1936/4A	1,8

