


1928DA reversible impact wrench



- Double hammer impulse device
- Sturdy and compact; high torque
- Reversible lever
- Three power adjustable positions
- Exhaust through handle
- Slip-proof ergonomic handle

Free speed	5,000 rpm
Max. torque	1.695 Nm
Bolt capacity	Cl 8.8 M30 ● 46 mm
Bolt capacity	Cl 12.9 M27 ● 41 mm
Air inlet	3/8" GAS
Working pressure	6,2 bar
Internal hose size (Ø)	10 mm
Mean air consumption	240 l/min
Weight	4,3 kg

	art.	■	ⓘ
019280022	1928DA	3/4	4,3

