

## 1932B13

## Reversible drill



- Powerful and sturdy
- Autochuck
- Auxiliary handle
- Reversible lever
- Slip-proof handle
- Exhaust through handle

 1,6 kg

|                               |                     |
|-------------------------------|---------------------|
| <b>Free speed</b>             | <b>400 rpm</b>      |
| <b>Chuck capacity</b>         | <b>1,5÷13 mm</b>    |
| <b>Power</b>                  | <b>0,34 kW</b>      |
| <b>Spindle thread</b>         | <b>1/2" - 20UNC</b> |
| <b>Air inlet</b>              | <b>1/4" GAS</b>     |
| <b>Operating pressure</b>     | <b>6,2 bar</b>      |
| <b>Internal hose size (Ø)</b> | <b>10 mm</b>        |
| <b>Mean air consumption</b>   | <b>180 l/min</b>    |
| <b>Weight</b>                 | <b>1,6 kg</b>       |

|  | art.    |  |
|---------------------------------------------------------------------------------|---------|-----------------------------------------------------------------------------------|
| 019320004                                                                       | 1932B13 | 1,6                                                                               |

