

1936/5A
Angle grinder

CE

- Extremely compact and handy
- Air governor for automatically controlling top speed
- Right-hand/left-hand auxiliary handle
- Spindle lock button
- Accessory for quickly changing discs
- Safety cap can be quickly adjusted in nine different positions through quick release
- Rear exhaust

Free speed	10,000 rpm
Grinding disc size	125 mm
Power	0,66 kW
Spindle thread	M14
Air inlet	1/4" GAS
Working pressure	6,2 bar
Ø internal hose size	10 mm
Mean air consumption	390 l/min
Weight	1,9 kg

	art.	
019360025	1936/5A	1,9

