

1949P

## Progressive mini blow gun

- Hard-wearing, shockproof composite material body
- Quick nozzle fixing system
- Airflow can be adjusted through ring nut rotation

### Pocket-size!

|                            |                |
|----------------------------|----------------|
| Brass threaded insert      | 1/4" GAS       |
| Working pressure           | 6÷8 bar        |
| Maximum operating pressure | 15 bar         |
| Mean air consumption       | 280 l/min      |
| Operating temperature      | -10 °C ÷ 85 °C |
| Weight                     | 70 g           |

|  | art.  |  |
|---------------------------------------------------------------------------------|-------|-----------------------------------------------------------------------------------|
| 019490031                                                                       | 1949P | 70                                                                                |

