

1933L

## long spindle die grinder

CE

- Collect chuck, Ø 3 mm and 6 mm

|                               |            |
|-------------------------------|------------|
| <b>Free speed</b>             | 25,000 rpm |
| <b>Chuck capacity</b>         | 3 - 6 mm   |
| <b>Power</b>                  | 0,20 kW    |
| <b>Air inlet</b>              | 1/4" GAS   |
| <b>Working pressure</b>       | 6,2 bar    |
| <b>Internal hose size (Ø)</b> | 10 mm      |
| <b>Mean air consumption</b>   | 270 l/min  |
| <b>Weight</b>                 | 670 g      |

|  | art.  |  |
|---------------------------------------------------------------------------------|-------|-----------------------------------------------------------------------------------|
| 019330015                                                                       | 1933L | 670                                                                               |

