

1937N20

20-mm pneumatic belt sander

CE

- High removal capacity based on 20-mm belt
- Antislip handle
- Quick-to-replace belt
- Adjustable swivel sanding arm
- Belt safety guard
- Swivel air inlet
- Silenced rear exhaust
- Safety lever device

1,6 kg

Easy to handle, safe

Free speed	16,000 rpm
Power	0,45 kW
Belt size	20x520 mm
Air inlet	1/4" GAS
Working pressure	6,2 bar
Internal hose size (Ø)	10 mm
Mean air consumption	400 l/min
Weight	1,6 kg



	art.		kg
019370051	1937N20	1,6	1,6