

1937N10
10-mm pneumatic belt sander

CE

- Sander for belts 10x330 mm
- Antislip handle
- Quick-to-replace belt
- Adjustable swivel sanding arm
- Belt safety guard
- Swivel air inlet
- Silenced rear exhaust
- Safety lever device

Ideal for jobs in small areas

Free speed	20,000 rpm
Power	0,37 kW
Belt size	10x330 mm
Air inlet	1/4" GAS
Working pressure	6,2 bar
Internal hose size (Ø)	10 mm
Mean air consumption	374 l/min
Weight	0,9 kg

	art.	
019370041	1937N10	0,9

