

1949T

Telescopic progressive blow gun

- Hard-wearing, shockproof composite material body
- Telescopic steel swivel tube: 165 mm ÷ 300 mm

Aluminium threaded insert	1/4" GAS
Operating pressure	6÷8 bar
Maximum operating pressure	15 bar
Mean air consumption	144 l/min
Operating temperature	-20°C ÷ 70°C
Weight	190 g

	art.	1949T
019490040	1949T	190

