


867RTX/L
bits for Tamper Resistant Torx® head screws


- 10 mm hexagon drive.
- For manual, electric and pneumatic screwdrivers.

	art.	⊕	L	⚙
008670550	867RTX-L 20	T20	75	42,6
008670555	867RTX-L 25	T25	75	43,2
008670560	867RTX-L 30	T30	75	43,4
008670565	867RTX-L 40	T40	75	44
008670570	867RTX-L 45	T45	75	45
008670575	867RTX-L 50	T50	75	45,6
008670580	867RTX-L 55	T55	75	47,6

