


Technical data sheet

Cone cable gland, metric thread, cutting ring, nickel-plated

Item no. 2083728



Cable gland with hexagonal intermediate connector, shape C4, to DIN 46320 with metric connection thread to DIN EN 60423 and ISO 68. Pressure rings made of electrogalvanised and transparently passivated steel. NR/SBR sealing ring.
Protection rating: with connection thread sealing ring IP 65, without connection thread sealing ring IP 54.

With cutting ring.

* Prices according to DEL notation.



CuZn	Brass
N	Nickel-plated

Master data

Item no.	2083728
Type	162 MS M40
Description 1	Cable gland
Description 2	with cutting ring
Dimension	M40
Material	Brass
Material symbol	CuZn
Surface	Nickel-plated
Surface symbol	N
Smallest sales unit (VG)	10,00 Piece
Weight	14,88 kg/100 pc.


Technical data sheet

Cone cable gland, metric thread, cutting ring, nickel-plated

Item no. 2083728



Technical data



Dimension E	54,00 mm
Dimension L	29,00 mm
Dimension L max.	29,00 mm
Dimension L1	8,50 mm
Dimension L2	29,00 mm
Dimension L3	3,50 mm
SW 1	50,00 mm
SW 2	47,00 mm
Type of seal	Cuttable sealing ring
Bend protection	☐
Sealing range D	24,00 - 31,00 mm
explosion-proof	☐
Flat cable threaded connection	☐
For Ex zone	Without
Thread	M40 x 1,5
Thread type	Metric
Thread length	8,50 mm
Fibre-glass reinforced	☐
Halogen-free	☐
Multiple sealing insert	☐
With locknut	☐
Impact-resistant	☐
Protection rating	IP65
Strain relief option	☐