



Dept
Qty
DC 1
ED 1
IE 1
ISO 1
PD 1
R&D 1
SD 1
QA 1
QC 1
QE 1


The information provided herein is from CONNELY Electronic Co., Ltd. and is confidential. Any disclosure to a party other than the recipient is prohibited. The intellectual properties and its rights, including but not limited to the design, structure, and appearance, of the product are strictly prohibited without prior written consent from CONNELY. All intellectual properties provided herein are for reference purposes only and does not constitute authorization of its use in any format or manner. CONNELY may enforce its intellectual property rights at its own discretion; failures or delays to exercise such rights does not constitute a waiver of such rights.




Type 1(1000V Flat type)



Type 2(1000V Round type)



Type 3(1500V Round type)



Type 4(Multifunction type)

REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	JLZ 06/02/23'		

Notes:

Specifications:

1. Voltage Rating:1000V&1500V.
2. Temperature: -40°C~+85°C.

Materials:

1. Insulating material:PC.

Product Number Code:

DS1162-20 - X X

Spanner type

- 1: Type 1
- 2: Type 2
- 3: Type 3
- 4: Type 4

Spanner color

- B: Black(For Type 4)
L: Blue



(Series Image-Reference Only)

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION		TITLE		
X.	±0.60	X.	±5°	UNITS	mm	MC4 Spanner Tool		
.X	±0.38	.X	±3°	SHEET SIZE	A4	SERIES	DS1162-20 SERIES	
.XX	±0.25	.XX	±2°	 晨翔电子有限公司 CONNFLY CONNFLY ELECTRONIC CO. LTD				
DRAWING TYPE		CUSTOMER						
SCALE	1:1	SHEET	1 OF 1					
DRAWING NO.	C-DS1162-20-XX-A							

晨翔电子有限公司
CONNELY CONNELY ELECTRONIC CO. LTD