



EG130 – Low temperature glue gun

EG130LT, standing for “Low Temperature”, is a glue gun specially designed to be used on sensitive materials, along with special oval glue sticks available in transparent or glitter colours. Its maximum temperature is 130°C to ensure no damage on sensitive materials such as polystyrene, flowers (fresh or artificial), thin papers etc.

Release your creative side and create your own unique decorations!



Features:

- Low temperature: 130°C – for fragile materials, no damage
- Silicone protection nozzle – for safety
- Standard nozzle, diam 1.8mm - For a fine streak of glue
- Improved work stand – for better stability
- Soft trigger and good handling - for comfortable use

Specifications:

- Glue sticks Oval 9mm
- Maxi Temperature..... 130°C
- Heating time 3 to 6 min
- Power 15 (100W)
- Working voltage..... 220V-240V/50Hz
- Tool Weight 0,245 kg



Description	Packaging	Dimensions	Art. No	EAN	Inner/Outer
EG130LT D9 – West EU	Blister	155*170*37	5000435	3221633029191	5/20pcs
EG130LT D9 – East EU	Blister	155*170*37	5000445	3221633029320	5/20pcs
EG130LT D9 – UK plug	Blister	155*170*37	40303000	3221633030005	5/20pcs

ISABERG RAPID AB, BOX 115
SE-335 03 HESTRA, SWEDEN
www.rapid.com

Rapid®
SVENSK EFFIXITY