



EG360 Pro-Industrial glue gun

Mechanical thermostat for temperature regulation from 120°C to 230°C to work with low and high temperature glue sticks. Fast heating time of 2min.

EG360 is equipped with a heater system of 300 Watts, a very accurate trigger mechanism allowing the best ratio pressure/transfer into the melting chamber. High glue output up to 1800 g/h providing good performances for intensive work.

Applications : PVC, Cables and tiles sealing, Electronics and electrics, Furniture and wood working, manual and corrugated carton sealing, trade exhibits and installation...

Features:

- Well-balanced
- High glue output for intensive works
- Interchangeable nozzle according to applications
- Smooth-4 fingers trigger for best comfort and reducing effort required
- For both low and high temperature glue sticks
- Long cord for flexibility and mobility
- Mobile and fixed stand for best efficiency
- Main switch ON/OFF

Specifications:

- Power rating : 300W
- Working Voltage : 220-240V
- Glue Output : 40g/min - 1800gr/h
- Heating Time(195°C) : 2 min
- Cord Length : 2.50m
- Temperature settings : 120-145-170-195-230°C
- Nozzle: Ø 3.0mm
- Dim : 210*265*50mm
- Weight : 0.70kg



Description	Packaging	Art. No	EAN	Outer
EG360 EU plug	Cardboard box	5000328	4051661011689	5 pcs
EG360 CH plug	Cardboard box	5000566	4051661019074	5 pcs

**ISABERG RAPID AB, BOX 115
SE-335 03 HESTRA, SWEDEN
www.rapid.com**

Rapid®
SVENSK EFFIXITY