

Torque screwdriver with key handle TorqueFix® Key



permanently pre-set torque limit

28360

Order-No.	Nm	7.5%	mm	mm	mm	mm
38616	0.5	6	4.0	68	50	1
38617	0.6	6	4.0	68	50	1
38618	0.9	6	4.0	68	50	1
38556	1.1	6	4.0	68	50	1
38800	1.2	6	4.0	68	50	1
38619	1.4	6	4.0	68	50	1
38557	2.0	6	4.0	68	50	1
38620	2.5	6	4.0	68	50	1
38621	3.0	6	4.0	68	50	1
38558	3.8	6	4.0	68	50	1
38622	4.0	6	4.0	68	50	1

DIN EN ISO 6789.

Interchangeable blade



Hexagon for torque screwdriver with key handle

283693

Order-No.	mm	mm	mm	mm	mm	mm
38801	1.5	4	75	20	0.9	10
38802	2.0	4	75	20	1.8	10
38803	2.5	4	75	20	3.8	10
38804	3.0	4	75	20	5.5	10
38805	4.0	4	75	20	8.0	10

Interchangeable blade



TORX® for torque screwdriver with key handle

283695

Order-No.	mm	mm	mm	mm	mm	mm
38806	T6	4	75	20	0.6	10
38807	T7	4	75	20	0.9	10
38808	T8	4	75	20	1.3	10
38809	T9	4	75	20	2.5	10
38810	T10	4	75	20	3.8	10
38811	T15	4	75	20	5.5	10
38812	T20	4	75	20	8.0	10
38813	T25	4	75	20	8.0	10

Interchangeable blade



TORX PLUS® for torque screwdriver with key handle

283696

Order-No.	mm	mm	mm	mm	mm	mm
38814	6IP	4	75	20	0.8	10
38815	7IP	4	75	20	1.3	10
38816	8IP	4	75	20	2.0	10
38817	9IP	4	75	20	3.0	10
38818	10IP	4	75	20	4.5	10
38819	15IP	4	75	20	6.6	10
38820	20IP	4	75	20	8.0	10
38821	25IP	4	75	20	8.0	10