

**1/2"****1/4"****60 pcs. incl. L Boxx**

33397

Order-No.	
44685	1
	Ratchet wrench for nut drivers 1/4" switchable 1/4" x 128 mm (44666) / 1/2" x 257 mm (44709)
	Nut driver insert 1/4" hexagon head 4.0 mm (44669) / 5.0 mm (44670) / 5.5 mm (44671) / 6.0 mm (44672) / 7.0 mm (44673) / 8.0 mm (44674) / 9.0 mm (44675) / 10.0 mm (44676) / 11.0 mm (44678) / 12.0 mm (44679) / 13.0 mm (44680) / 14.0 mm (44681)
	Nut driver insert 1/2" double hex 10.0 mm (44715) / 11.0 mm (44716) / 12.0 mm (44717) / 13.0 mm (44718) / 14.0 mm (44719) / 15.0 mm (44720) / 16.0 mm (44721) / 17.0 mm (44722) / 18.0 mm (44723) / 19.0 mm (44724) / 21.0 mm (44726) / 22.0 mm (44727) / 24.0 mm (44729) / 27.0 mm (44732) / 30.0 mm (44735) / 32.0 mm (44737) / 34.0 mm (44738)
	Extension 1/4" for nut driver inserts 75 mm (44667) / 150 mm (44668)
	Extension 1/2" for nut driver inserts 150 mm (44711) / 250 mm (44712)
	Universal joint with ball Internal square, square head 1/4" (44682) / 1/2" (44739)
	Screwdriver with bit holder SoftFinish® magnetic 1/4" 112 mm (32160)
	Bit holder CentroFix Force mechanically lockable 1/4", magnetic in box 60 mm (39133)
	Bit Standard 25 mm Slotted 1/4" C6,3 4.5 mm (01623) / 5.5 mm (01624) / 6.5 mm (01626)
	Bit Standard 25 mm Phillips 1/4" C6,3 PH1 (01657) / PH2 (01658)
	Bit Standard 25 mm Pozidriv 1/4" C6,3 PZ1 (01688) / PZ2 (01689) / PZ3 (01690)
	Bit Standard 25 mm TORX® 1/4" C6,3 T10 (01716) / T15 (01717) / T20 (01718) / T25 (01719) / T27 (01720) / T30 (01721) / T40 (01722)
	Bit Standard 25 mm Hexagon 1/4" C6,3 3.0 mm (01705) / 4.0 mm (01706) / 5.0 mm (01707) / 6.0 mm (01708)
	Tool shaft with ball Square, Internal hexagon 1/4" C6,3 (01933)
	L-BOXX

Based on DIN 3124