

Ratchet wrench set insulated, 1/4"



21-pcs. in case

7209NK2001

Order-No.	
43025	1

Fastening / jamming

	Ratchet wrench insulated for nut drivers 1/4" switchable (43054)
	Insulated extension 1/4" square adapter for nut driver inserts, insulated 75 mm (43059) / 150 mm (43060)
○	Insulated nut driver insert 1/4" hexagon head 4.0 mm (43088) / 5.0 mm (43089) / 5.5 mm (43090) / 6.0 mm (43091) / 7.0 mm (43092) / 8.0 mm (43093) / 9.0 mm (43094) / 10.0 mm (43095) / 11.0 mm (43096) / 12.0 mm (43097) / 13.0 mm (43098) / 14.0 mm (43099)
●	Insulated nut driver insert 1/4" internal hexagon 3.0 mm (43109) / 4.0 mm (43110) / 5.0 mm (43111) / 6.0 mm (43112) / 8.0 mm (43113)

Storage

case
IEC 60900

Single open-end spanner set, insulated 6-32 mm



21-pcs. incl. case

5590NT20

Order-No.	
43022	1

○	Single, insulated open-end spanner 6.0 mm, 90 mm (43026) / 7.0 mm, 90 mm (43027) / 8.0 mm, 100 mm (43028) / 9.0 mm, 100 mm (43029) / 10.0 mm, 110 mm (43030) / 11.0 mm, 110 mm (43031) / 12.0 mm, 130 mm (43032) / 13.0 mm, 135 mm (43033) / 14.0 mm, 145 mm (43034) / 15.0 mm, 150 mm (43035) / 16.0 mm, 160 mm (43036) / 17.0 mm, 160 mm (43037) / 18.0 mm, 175 mm (43038) / 19.0 mm, 175 mm (43039) / 22.0 mm, 195 mm (43040) / 24.0 mm, 225 mm (43041) / 27.0 mm, 250 mm (43042) / 30.0 mm, 290 mm (43043) / 32.0 mm, 310 mm (43044)
○	Adjustable spanner electric Adjustable between 0-30 mm 250 mm (43061)

Storage

case
DIN EN IEC 60900