

UPS power strip, 3 Schuko sockets, fused switch, 10 A, C14 plug, 0.6 m cable, black

EG-PSU3-01



Features

- 3-socket power strip with C14 plug
- Suitable for use with e.g. a UPS with C13 power outlets
- Fused power switch

Specifications

Input voltage: up to 230 VAC, 50 – 60 Hz, C14 plug
Sockets: Schuko, 3 pcs
Maximum load current: 10 A
Power cord: 0.6 m, 3G1.0mm²
Working temperature range: from 0 to +40 °C
Dimensions: 175 x 42 x 38 mm (body only)
Net weight: 0.145 kg

Packaging

Q'ty in crtn, pcs
Crtn volume, CUM
Crtn weight, kgs
Individual package size LxWxH:
Carton size LxWxH:
Country of origin
Barcode
Customs code

50
0.057
11.13
210x80x40 mm
460x280x440 mm
CN
8716309102674
8544429090

Certificates

