



Audio-video cord

Model: **AK-HD-30S**



Product code	AK-HD-30S
Product type	Audio-video cord
Series	HDMI
Signal frequency	4K@120Hz, 8K@60Hz
CEC function	Yes
Directivity	Two-way
Cable length	3 m
The cable plug #1	Male connector HDMI
The cable plug #2	Male connector HDMI
Shielded cable	Yes
Version	HDMI 2.1
Plated plugs	Gold
Cable material	Copper
Product color	Black
Temperature	5 - 50 °C
Package	UniBag
Product size (L x W x H)	150 x 210 x 30 mm
Net weight	195 g
Gross weight	202 g
REACH compatibility	Yes
EAN code	5901720138101
Warranty	24 months
Bandwidth	48 Gbit/s



Description

The **3-meter Akyga® AK-HD-30S HDMI 2.1 cable** is the perfect solution for those seeking the highest quality audio/video connection. This cable is made in accordance with the **HDMI 2.1 standard**, allowing users to enjoy high-quality images in **Ultra HD 4K and 8K resolution**, as well as full-range multichannel audio. The Akyga®AK-HD-30S HDMI 2.1 cable provides incredibly fast data transmission at a **bandwidth of up to 48 Gbps**, enabling smooth playback of content in the highest quality, including **HDR** (High Dynamic Range), **Dolby Vision**, and **Deep Color**. Additionally, this cable is reinforced with a braided sleeve, making it extremely durable and reliable.

By utilizing the **eARC** (Enhanced Audio Return Channel) technology, this HDMI cable enables the transmission of studio-quality audio without any loss, which will particularly satisfy home cinema enthusiasts and avid gamers. Furthermore, this cable supports features such as Dynamic HDR and Variable Refresh Rate (VRR), resulting in smoother and more responsive gaming experiences.