



Figure similar

MLFB-Ordering data

6SL3210-5FB10-4UF1

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data		Ambient conditions	
Input		Cooling	natural convection
Number of phases	1 AC	Installation altitude	1000 m
Line voltage	200 ... 240 V +10 % -15 %	Ambient temperature	
Line frequency	45 ... 66 Hz	Operation	0 ... 45 °C
Output		Storage	-40 ... 70 °C
Rated power	0.40 kW	Relative humidity	
Rated current (IN)	2.60 A	Max. operation	90 %
Max. output current	7.80 A	Standards	
Inputs / outputs		Compliance with standards	CE, KC, cULus, EAC, C-Tick (RCM)

Standard digital inputs

Number	4
--------	---

Digital outputs

Number	2
--------	---

Mechanical data	
Degree of protection	IP20 / UL open type
Size	FSB
Net weight	1.25 kg
Width	55.0 mm
Height	170.0 mm
Depth	170.0 mm