



SIMATIC DP, CM PROFIBUS DP for ET 200SP CPU module with PROFIBUS DP interface (9-pole D-sub socket) DP master for 125 DP slaves DP slave,

General information	
Product type designation	CM PROFIBUS DP
HW functional status	FS04
Engineering with	
• STEP 7 TIA Portal configurable/integrated from version	V13 Update 3
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
1. Interface	
Interface types	
• RS 485	Yes
Protocols	
• PROFIBUS DP master	Yes
• PROFIBUS DP slave	Yes
• SIMATIC communication	Yes
PROFIBUS DP master	
• Number of DP slaves, max.	125
Services	
— PG/OP communication	Yes
— Equidistance	No
— Isochronous mode	No
— Activation/deactivation of DP slaves	Yes
PROFIBUS DP slave	
• Transmission rate, max.	12 Mbit/s
• automatic baud rate search	Yes
• Address area, max.	120
• User data per address area, max.	128 byte
Services	
— PG/OP communication	Yes; Only with active interface
— Routing	Yes; Only with active interface
— S7 communication	Yes; Only with active interface
— Direct data exchange (slave-to-slave communication)	Yes; No subscriber possible - only passive publisher
— DPV1	Yes
Transfer memory	
— Inputs	244 byte
— Outputs	244 byte
Interface types	

RS 485	
• Transmission rate, max.	12 Mbit/s
• Cable length, max.	100 m
Protocols	
SIMATIC communication	
• S7 routing	Yes
• Data record routing	Yes
Interrupts/diagnostics/status information	
Diagnostics function	Yes
Diagnostics indication LED	
• for module diagnostics	Yes; green/red DIAG LED
Potential separation	
between backplane bus and interface	Yes
Ambient conditions	
Ambient temperature during operation	
• horizontal installation, min.	-25 °C; No condensation
• horizontal installation, max.	60 °C
• vertical installation, min.	-25 °C; No condensation
• vertical installation, max.	50 °C
Altitude during operation relating to sea level	
• Installation altitude above sea level, max.	5 000 m; Restrictions for installation altitudes > 2 000 m, see manual
Dimensions	
Width	35 mm
Height	117 mm
Depth	75 mm
Weights	
Weight, approx.	80 g

last modified: 10/3/2023 