

# Spring-loaded test probe

## GKS-100 307 150 A 4000

Item GKS-100-0170



GO TO PRODUCT

**ingun**<sup>®</sup>

Partner for Future Technology

### General data

|                                |                         |
|--------------------------------|-------------------------|
| Product group                  | Accessories (GKS / ADA) |
| Sub-product group              | Interface block probes  |
| Series                         | GKS-100                 |
| Grid                           | 2.54 mm [100 mil]       |
| Contacting from                | Pad, via                |
| Magnetic                       | Yes                     |
| Installation type              | Plug-in                 |
| Quick-exchange system          | Yes                     |
| Adjustable installation height | No                      |
| Non-rotating                   | No                      |
| Compatible receptacle(s)       | KS-100                  |
| Min. temperature               | - 40 °C [- 104 °F]      |
| Max. temperature               | + 80 °C [+ 176 °F]      |
| RoHS-compliant                 | RoHS-3;6c               |

### Electrical data


|                                       |          |
|---------------------------------------|----------|
| Current load capacity / rated current | 8 A      |
| Typical resistance (Ri)               | <20 mOhm |

### Mechanical data

|                                |                   |
|--------------------------------|-------------------|
| Total length                   | 33.4 mm [1.31 in] |
| Barrel diameter                | 1.37 mm [.053 in] |
| Maximum stroke                 | 6.35 mm [.25 in]  |
| Spring pre-load                | 1.18 N [4.24 ozf] |
| Collar height                  | 00                |
| Spring force at working stroke | 4 N [14.3 ozf]    |
| Recommended working stroke     | 4.3 mm [.169 in]  |

### Tip style data

|                    |                                      |
|--------------------|--------------------------------------|
| Tip style          | 07 90° 3-edged chisel, self-cleaning |
| Tip diameter       | 1.5 mm [.059 in]                     |
| Tip style surface  | A gold                               |
| Tip style material | 3 CuBe                               |



# Spring-loaded test probe


## GKS-100 307 150 A 4000

Item GKS-100-0170



**ingun**<sup>®</sup>

Partner for Future Technology



### INGUN Prüfmittelbau GmbH

Max-Stromeyer-Straße 162  
78467, Constance, Germany  
Phone +49 7531 8105-0  
Customer hotline +49 7531 8105-888  
Fax +49 7531 8105-65  
info@ingun.com



Prices and delivery times on request.  
Technical changes reserved. 09/23 EN

Learn more about  
Test probes

