

ANGULAR HDMI V2.1, 1.8 M CABLE



8K

RESOLUTION

HDR

DYNAMIC

144/
240Hz

REFRESH RATE

VRR

GAME MODE

EARC

ENHANCED AUDIO
RETURN CHANNEL

DOLBY

TRUE HD



EN TECHNICAL SPECIFICATION

Version:	HDMI 2.1 Ultra High Speed HDMI v2.1 cable supports resolutions up to 8K@60Hz, 4K@120Hz and FullHD@240Hz
Length:	1.8m
Plugs:	2x HDMI A, male, 24k gold-plated
Supports:	- Data transfer rate up to 48 Gbps - Dynamic HDR, Dolby Vision, 3D Video, Game Mode VRR, Display Stream Compression, Deep Color, CEC - Consumer Electronics Control - eARC - Enhanced Audio Return Channel, Dolby TrueHD, DTS-HD Master Audio - Backwards compatible with HDMI 1.3, 1.4, 2.0 versions

OFC - oxygen-free copper wires with a high purity (99,96%)

Protected against external interference - full shielding of signal wires

Cotton braided

Organizer for easy cable laying included

