




A

B

C

D

E

A


B

C



D

E


FOR 客户名称	APPROVED 客户确认签字	ATTN 销售负责人



L: MOMENTARY IS 36.5 Max.
LATCHING IS 43 Max.




PANEL CUTOUT



SEAL RING

SCHEMATIC



DOUBLE-BREAKPOINT SNAP-ACTION CONTACT SWITCH WITH FOUR TERMINALS

PART NUMBER:LAS1GQH-11■/L/S/※

"■"	OPERATION MODE	"※"	IP CLASS
NO LETTER	MOMENTARY	NO LETTER	IP65
Z	LATCHING	FP	IP67(MOMENTARY)

SPECIFICATIONS:

- 1.SWITCH RATING: Ui:250V, Ith:20A.
- 2.MECHANICAL LIFE: ≥1,000,000 cycles.
- 3.ELECTRICAL LIFE: ≥50,000 cycles.
- 4.INITIAL CONTACT RESISTANCE: ≤50mΩ.
- 5.INSULATION RESISTANCE: ≥100MΩ(500VDC).
- 6.DIELECTRIC STRENGTH: 1,500V, RMS 50Hz, 1min.
- 7.OPERATING TEMPERATURE: -25℃~ +55℃(NO FREEZING, KEEP THE AIR FLOWING AROUND PUSHBUTTON).
- 8.OPERATING FORCE: ABOUT 4N(IP65), ABOUT 5N(IP67).
- 9.OPERATING TRAVEL: ABOUT 3mm.
- 10.TORQUE: 0.6Nm Max. APPLIED TO NUT.
- 11.FRONT PANEL PROTECTION DEGREE: IP65(IP67 MOMENTARY CAN BE CUSTOMIZED); IK09.
- 12.TERMINAL TYPE: SCREW TERMINAL.
- 13.GENERAL TOLERANCE:0-18mm=±0.25, 18-80mm=±0.52.

MATERIALS:

- 1.CONTACT: SILVER ALLOY.
- 2.BUTTON: STAINLESS STEEL.
- 3.BODY: STAINLESS STEEL.
- 4.BASE: PA.

BRAND 品牌		红波按钮制造有限公司			
ONPOW 欧宝龙®		ONPOW PUSH BUTTON MANUFACTURE CO.,LTD.			
TITLE 名称	LAS1GQ SERIES ANTI-VANDAL PUSH BUTTON			UNIT 单位	mm
DWG NO. 图号	LAS1GQH-11L			SCALE 比例	1.2 : 1
FILE NAME 档案名称	LAS1GQ-11L .DWG	DRAWN 制图	HCP 2023/10/28	SHEET 张	1/1
				REV. 更改	1