



SYM	DESCRIPTION	APPROVED	DATE
1			
2			
3			
4			



BNC video connector cable (RG59), double shielded

Connectors: 2x BNC male
Contacts: nickel-plated (gold-plated pins)
Conductor area: 0.324 mm²
AWG: 22
Composition of conductor: 1 x 0.643 mm
Conductor material: CCS
Insulation material: PE
Jacket material: PVC
Conductor resistance: 300 ± 10 Ω/km
Shielding: 30 % coverage
Capacitance: 58 ± 5 pF/m
Cable OD: 6.0 ± 0.2 mm
Weight: 41 ± 2 g/m

SYM	Name	Description	Remarks	Tolerance (mm)			
				Wire harness size L(mm)	Trunk	Protection tube	Positioning space
13				L ≤ 200	+20 -10		±5
12				200 < L ≤ 500	+25 -10		±5
11				500 < L ≤ 1000	+40 -20		±10
10				1000 < L ≤ 2000	+60 -30		±20
9				2000 < L ≤ 3000	+80 -50		±30
8				3000 < L ≤ 5000	+100 -80		±40
7				L > 5000	+120 -100		±50
6							
5							
4							
3							
2							
1							



APPROVED	Shen Juan		
CHECKED	Li Jie		
DRAWN	Zhang Yining	Customer :	Date : 2023-10-19
UNIT	mm	DRAWING NO.	BNC-075-1.0
REV	1	CUSTOMER NO.	PAGE: 1/1