



SYM	DESCRIPTION	APPROVED	DATE
1			
2			
3			
4			



BNC connector cable (RG58), shielded

Connectors:	2x BNC male
Contacts:	nickel-plated (gold-plated pins)
Conductor area:	0.636 mm ²
AWG:	20
Composition of conductor:	1 x 0.90 mm
Conductor material:	CCS
Insulation material:	PE
Jacket material:	PVC
Conductor resistance:	500 ± 10 Ω/km
Shielding:	35 % coverage
Capacitance:	54 ± 5 pF/m
Cable OD:	5.0 ± 0.2 mm
Weight:	30 ± 2 g/m

SYM	Name	Description	Remarks	Tolerance (mm)			
				Wire harness size L(mm)	Trunk	Protection tube	Positioning space
13				L≤200	+20 -10		±5
12				200<L≤500	+25 -10		±5
11				500<L≤1000	+40 -20		±10
10				1000<L≤2000	+60 -30		±20
9				2000<L≤3000	+80 -50		±30
8				3000<L≤5000	+100 -80		±40
7				L>5000	+130 -80		±40
6							
5							
4							
3							
2							
1							



APPROVED	Shen Juan		
	Li Jie		
CHECKED	Zhang Yining	Customer :	Date : 2023-10-19
UNIT	mm	DRAWING NO.	BNC-050-2.0
REV	1	CUSTOMER NO.	PAGE: 1/1